



材質	T	
	0.5	1
不銹鋼(SUS304)	+0.1 0	+0.1 0
黃銅(C2600P)		

SUS		黃銅		對應軸承	d	D	T	備註	包裝
品號	庫存	品號	庫存						
RS5016022050	△	RB5016022050	△	608	16	22	0.5	外 圈 用	5pcs 袋
RS5016022100	△	RB5016022100	△	636					
RS5016022100	△	RB5016022100	△	6900					
RS5018024050	△	RB5018024050	△	628	18	24	0.5		
RS5018024100	△	RB5018024100	△	6802					
RS5018024100	△	RB5018024100	△	6901					
RS5020026050	△	RB5020026050	△	6000	20	26	0.5		
RS5020026100	△	RB5020026100	△	6803					
RS5020026100	△	RB5020026100	△						
RS5021028050	△	RB5021028050	△	638	21	28	0.5		
RS5021028100	△	RB5021028100	△	6001					
RS5021028100	△	RB5021028100	△	6902					
RS5023030050	△	RB5023030050	△	6200	23	30	0.5		
RS5023030100	△	RB5023030100	△	6903					
RS5023030100	△	RB5023030100	△						
RS5025032050	△	RB5025032050	△	6002	25	32	0.5		
RS5025032100	△	RB5025032100	△	6201					
RS5025032100	△	RB5025032100	△	6804					
RS5028035050	△	RB5028035050	△	6003	28	35	0.5		
RS5028035100	△	RB5028035100	△	6202					
RS5028035100	△	RB5028035100	△	6300					
RS5029037050	△	RB5029037050	△	6301	29	37	0.5		
RS5029037100	△	RB5029037100	△	6805					
RS5029037100	△	RB5029037100	△	6904					
RS5032040050	△	RB5032040050	△		32	40	0.5		
RS5032040100	△	RB5032040100	△	6203					
RS5032040100	△	RB5032040100	△						
RS5035042050	△	RB5035042050	△	6004	35	42	0.5		
RS5035042100	△	RB5035042100	△	6302					
RS5035042100	△	RB5035042100	△	6806					
RS5040047050	△	RB5040047050	△	6005	40	47	0.5		
RS5040047100	△	RB5040047100	△	6204					
RS5040047100	△	RB5040047100	△	6303					
RS5042052050	△	RB5042052050	△	6807	42	52	0.5		
RS5042052100	△	RB5042052100	△	6906					
RS5042052100	△	RB5042052100	△	6304					
RS5047055050	△	RB5047055050	△		47	55	0.5		
RS5047055100	△	RB5047055100	△	6006					
RS5047055100	△	RB5047055100	△	6907					
RS5052062050	△	RB5052062050	△	6007	52	62	0.5		
RS5052062100	△	RB5052062100	△	6206					
RS5052062100	△	RB5052062100	△	6305					
RS5058068050	△	RB5058068050	△	6908	58	68	0.5		
RS5058068100	△	RB5058068100	△	6008					
RS5058068100	△	RB5058068100	△						

PS. 備註

· 圖次1圖cs翻挑剝離之，可達到高精度的調整

訂貨：  交期：  天

RS5016022050

■層積型的使用方法

1. 圖0.05mm墊片環以接著劑貼合的層積墊片
2. 圖刀片輕輕挑起，一次一片翻挑之
3. 圖複2的動作，0.4→0.35→0.3...，以0.05mm為單位，作板厚的調整

